





PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 10mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
XHB-02AW	2.50	7.50
XHB-03AW	5.00	10.00
XHB-04AW	7.50	12.50
XHB-05AW	10.00	15.00
XHB-06AW	12.50	17.50
XHB-07AW	15.00	20.00
XHB-08AW	17.50	22.50
XHB-09AW	20.00	25.00
XHB-10AW	22.50	27.50
XHB-11AW	25.00	30.00
XHB-12AW	27.50	32.50
XHB-13AW	30.00	35.00
XHB-14AW	32.50	37.50
XHB-15AW	35.00	40.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		杨月旺		林月旺		料号		版本	A
			X.±0.25	X.'±2'	李攀进	李攀进	PART NO.	XHB-NAW-M	REV.	A		
							品 名	带扣弯针座	页 次	1/1		
							TITLE		SHEET			
							客户料号					
CUTM. NO.		深圳市富港科技有限公司										
			.X±0.20	.X'±1°	李攀进	李攀进	客户料号					
			.XX±0.15	.XX'±0.5°	罗观彬	罗观彬						
			.XXX±0.10	.XXX'±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1				