



RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE





NOTES:

1.MATERIAL:


- 1-1 HOUSING: THERMOPLASTIC,UL94 V-0. COLOR: BLACK
- 1-2 SHELL: STAINLESS STEEL T=0.20mm
- 1-3 CONTACT: COPPER ALLOY T=0.15mm

2.FINISH:

- 2-1 CONTACT: 1U" AU MIN. ON CONTACT AREA
- GOLD FLASH ON SOLD AREA
- 50u" NI MIN. UNDERPLATING OVER ALL



SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O




RECOMMENDED PCB LAYOUT TOP VIEW (TOLERANCE:±0.05)


RECOMMENDED MATAL MASK T=0.12mm

- SMT SOLDER AREA
- NO PATTERN AND VIA HOLE IN HTIS AREA


STEP 1 INSERT Micro-SIM CARD



STEP 2 PUSH THE SHELL



STEP 3 FINISH



GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30	X.° ±5°
.XX ±0.20	X.X° ±1°
.XXX ±0.10	X.XX° ±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.		TITLE:		
SIM30420-7P611-H15		1.5H 6PIN HINGE NANO SIM CARD CONNECTOR		
DESIGN: James	CUSTOMER	SIZE	UNITS	
CHED: Talen		A4	MM	
APPD: Sophia		SCALE	SHEET	
		N: A	1/1	