

1

2

3

4

5

6

7

8

A

B

C

D

E

F

G

H

Dept

Qty

晨翔3.96mm Wafer, VH TYPE, 7Pin母胶芯, 白色

DC

1

ED

1

IE

1

晨翔料号: I-DS1073-SCW007

ISO

1

PD

1

R&D

1

SD

1

QA

1

QC

1

QF

1

REV.

A

DESCRIPTION

NEW RELEASE

DRAWN

WPY 11/04/24'

CHECKED



APPROVED

28.12±0.3

23.76

5.7

7.4

10.4

13.6

电线规格

电线外径

截面积mm²

AWG

mm

0.33~0.83

22~18

1.7~3.0

GENERAL TOLERANCE

ANGLE TOLERANCE

PROJECTION



TITLE

X. ±0.60

X. ±5°

UNITS

mm

3.96mm Wafer, VH TYPE, 7Pin母胶芯, 白色

.X ±0.38

.X ±3°

SHEET SIZE

A4

SERIES

DS1073 SERIES

.XX ±0.25

.XX ±2°

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1073-XXXXX-A



晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

1

2

3

4

5

6

7

8

此提供的信息来自宁波晨翔电子有限公司并且是保密的。禁止向收件人以外的任何一方披露信息。本文包含的知识产权及其权利(包括但不限于商标, 专利, 版权, 商业机密和技术知识) 仅由晨翔或其附属公司拥有。未经晨翔事先书面同意, 严禁未经授权的使用或修改。此处提供的知识产权所有知识权仅供供参考, 并不构成以任何格式或方式使用其授权。晨翔可以自行决定强制执行其知识产权, 不履行或延迟行使这些权利并不构成对这些权利的放弃。

备注:

1. 电性说明:

1.1 耐压: 1000伏交流电一分钟

1.2 绝缘阻抗: 1000兆欧最小

1.3 接触电阻: 30毫欧最大

1.4 额定电流: 7安

2. 环境特性:

2.1 工作温度: -25~+80℃

3. 材料:

3.1 胶芯: PA66, 白色