

1 2 3 4 5 6 7 8

Dept	Qty	REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
DC	1	A	NEW RELEASE	WPY 11/04/24'		
ED	1					
FE	1					
ISO	1					
PD	1					
R&D	1					
SD	1					
QA	1					
QC	1					
QE	1					

晨翔3.96mm Wafer, VH TYPE, 6pin公头, 弯插, 白色, 全锡

晨翔料号: DS1073-6MRW6

备注:

- 电性说明:
 - 耐压: 1000伏交流电一分钟
 - 绝缘阻抗: 1000兆欧最小
 - 接触电阻: 最大30毫欧
 - 额定电流: 7安
- 环境特性:
 - 工作温度: -25~+85° C
- 材料:
 - 胶芯: PA66, 白色, 阻燃
 - 端子: 磷铜, 镀锡
- 产品符合欧盟RoHS环保要求

GENERAL TOLERANCE

X.	±0.60
.X	±0.38
.XX	±0.25

ANGLE TOLERANCE

X.	±5°
.X	±3°
.XX	±2°

DRAWING TYPE

CUSTOMER

SCALE

1:1

SHEET

1 OF 1

DRAWING NO.

C-DS1073-XXXXX-A

PROJECTION

UNITS

mm

SHEET SIZE

A4

TITLE

3.96mm Wafer, VH TYPE, 6pin公头, 弯插, 白色, 全锡

SERIES

DS1073 SERIES

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

1 2 3 4 5 6 7 8