



Main

Range of Product	Harmony Series K
Product or Component Type	Cam switch operating head
Component name	KAX
Product compatibility	Front mounting bodies 12 and 20 A Ø 22 mm hole
Cam switch head type	With bezel Ø 28.5 mm, metal
Type of operator	Black standard handle
Rotary handle padlocking	Without
Presentation of legend	With mat black

Complementary

Mechanical durability	1000000 cycles
CAD overall width	1.14 in (29 mm)
CAD overall height	1.14 in (29 mm)
CAD overall depth	0.98 in (25 mm)
Net Weight	0.09 lb(US) (0.04 kg)
Compatibility code	KAX

Environment

Protective treatment	TC
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Shock resistance	30 gn IEC 68-2-27
Vibration resistance	5 gn 10...150 Hz)IEC 68-2-6
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

Ordering and shipping details

Category	21446-9003 K CAM SWITCHES
Discount Schedule	CS1
GTIN	3389110980752
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	1.18 in (3.0 cm)
Package 1 Weight	1.27 oz (36.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	90
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.48 lb(US) (3.394 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------