





技术要求 Technical requirement:
使用条件 Conditions of Use: -40~55℃
额定负荷 Rated load: DC 30V0.5A
接触电阻 Contact resistance: <0.03Ω
绝缘电阻 Insulation resistance: >100MΩDC250V
耐压 Withstand voltage: AC500V(50Hz)/min
插拔力 Insertion: 3~20N
机械寿命 life: 5000次



线路板按照尺寸示意图

SCHEMATIC	
Model	DC-017
Center Pin	Ø2.0 mm
	Ø2.5 mm

	MATERIAL	PLATING
center pin	Brass	tin
terminal 1	Brass	tin
terminal 2	Sus	tin
terminal 3	Brass	tin
plastic	Pbt	

DSND		SCALE: N/A	MODEL TYPE: DC POWER JACK		
DWN		VIEW: 	PART NO.: DC-017-2.5A-2.0		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4			
PRECISION CO., LIMITED			WEIGHT	SHEET	REVISI
				1/1	A0

广东星坤科技股份有限公司

ΔX		日期					ANGULAR	IS
ΔX							≤ 4	±0.2
ΔX							4<≤ 16	±0.3
MARK		DESCRIPTION		DATE	REVISED	APPROVED	16<≤ 63	±0.4
							> 63	±0.5
UNSPECIFIED TOLERANCES								

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED