




* Screw : Copper Alloy,Nickel Plated,#4-40 UNC



Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚為1.2mm 以下

| Screw L=6.0 For Panel Thickness
| Between 1.2~2.0mm
| 適用板厚為1.2~2.0mm



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT:mm				TITLE	
TOLERANCE		D-SUB Conn.			
.X	±0.25	Panel Screw DB9P F Conn. F Pin			
.XX	±0.1	SCALE		SHEET	
.XXX	±0.05	Free		1 OF 1	
ANGLES	+1°	REV.	SIZE		QC
		A	A4		:Inspection Item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO SDB-09PFFP-SR8001	DRAWN BY DongYaLi	DATE 2006/12/15
DWG NO SDB-09PFFP-SR8001	CHECKED BY Simon	DATE 2006/12/15
CUSTOMER ALTW	APPROVED BY Max	DATE 2006/12/15