

# Product data sheet

## Characteristics

### ZA2BG4

key selector switch head - 2 pos. - stay put - withdrawal left/right-hand pos.



#### Main

Range of Product	Harmony XAC
Product or Component Type	Selector switch
Component name	ZA2
Product Compatibility	XACA

#### Complementary

Marking	Unmarked
Cap/operator or lens colour	Black
Mounting Location	Base of enclosure Front of enclosure
Sale per indivisible quantity	1
Net Weight	0.09 lb(US) (0.042 kg)

#### Environment

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508 EN/IEC 60204-32
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
Overvoltage category	Class II IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 EN 50102

#### Ordering and shipping details

Category	22460-PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
GTIN	3389110645323
Nbr. of units in pkg.	1
Package weight(Lbs)	1.73 oz (49.0 g)
Returnability	Yes
Country of origin	FR

#### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	1.18 in (3 cm)
Package 1 Length	2.36 in (6 cm)
Unit Type of Package 2	BB1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Number of Units in Package 2	10
Package 2 Weight	17.53 oz (497.0 g)
Package 2 Height	2.36 in (6 cm)
Package 2 width	9.45 in (24 cm)
Package 2 Length	7.09 in (18 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Weight	6.15 lb(US) (2.788 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------