









1	2	3	4	5	6	7	8	THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.
F				REV. A	ECN NO.	DATE 2006/03/01	SIGN DAVID	
E				B	LE3-710072	2006/12/20	DongYaLi	
D							Move 0-Ring To ZSE00100771	
C								
								
B				Note: * @C Important Dimension. * Waterproof Rate : IP68 IP68:1M of depth of water 24 hours (防水等級 IP68) (IP68:1米水深 24小時) * Do Mating Test After Glued 點膠後, 須作對插測試		Screw L=5.0 For Panel Thickness Under 1.2mm 適用板厚為 1.2mm 以下		
A	 15 Pin Female Connector PCB Pin Layout			* HD-SUB Conn. :Black Core , PBT * Plastic Jacket : Black , Nylon+GF * Pin : Copper Alloy , Gold Plated * Ring : Light Blue,Silicone * Screw : Copper Alloy,Nickel Plated,#4-40 UNC * The 180° Board Lock Needs To Connect The Iron Shell 180° 型支架需接鐵殼				
A	UNIT:mm TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	TITLE HD-SUB Connector 15Pin Female For Panel,PCB 180° Board Lock SCALE Free SHEET 1 OF 1 REV. B SIZE A4 @C :Inspection Item	Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO HDB-15PFFP-SA8001 DWG NO HDB-15PFFP-SA8001 CUSTOMER ALTW	DRAWN BY DongYaLi CHECKED BY Simon APPROVED BY Max	DATE 2006/12/20 DATE 2006/12/20 DATE 2006/12/20	8 FMW0702-01-01A2	