








NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING MATING AREA: GOLD FLASH over NICKEL
PLATING TERMINATION SIDE: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 12 - 14
- CONNECTOR IS PART MARKED: 3017W2SAM62A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance			
						dim. in mm	
					date	name	
				drawn	22.06.12	Schmidt	
				appd.	22.06.12	Koch	
				norm			
				d-old			
							
a	Original						
rev.	description	date	name				

scale:		2:1 (5:1)	
material:		see notes	
title: D-SUB COMBINATION FEMALE 17W2S SOLDER CUP			
dwg no:		DIN-A3	sh: 1
13K1A3991			
part no:		3017W2SAM62A10X	