

Product data sheet

Characteristics

KAC1S

Cam switch operating head, Harmony K, Ø 22mm, plastic, 45x45mm plate, matt black legend, key operated, Ronis 8R1



Main

Range of Product	Harmony Series K
Product or Component Type	Cam switch operating head
Component name	KAC
Product compatibility	Front mounting bodies 12 and 20 A Ø 22 mm hole
Cam switch head type	With front plate 45 x 45 mm
Type of operator	Key key 8R1
Rotary handle padlocking	Without
Presentation of legend	With mat black
Switching angle	45 ° 90 °

Complementary

Mechanical durability	1000000 cycles
CAD overall width	1.77 in (45 mm)
CAD overall height	1.77 in (45 mm)
CAD overall depth	2.72 in (69 mm)
Net Weight	0.14 lb(US) (0.063 kg)
Compatibility code	KAC

Environment

Protective treatment	TC
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Shock resistance	30 gn IEC 68-2-27
Vibration resistance	5 gn 10...150 Hz)IEC 68-2-6
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
GTIN	3389110483239
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.60 in (6.6 cm)
Package 1 Width	2.60 in (6.6 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	2.43 oz (69.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	60

Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	10.30 lb(US) (4.67 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------