





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
27	4.9	.300	1.40	17.60	30	C-2R
425	5.0	.500	2.30	28.91	15	C-2R
605	6.15	.500	3.40	42.74	15	C-2R

METRIC



THIRD ANGLE
PROJECTION

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

DRAWN BY
L. WENGSTROM

APPV'D BY DATE
QC 2/27/01

JKL

COMPONENTS CORPORATION

TITLE

G-4 1/2 MINIATURE SCREW BASE

SIZE
A

FSCM NO.
55335

DRAWING
NO.

SCREW BASE G-4 1/2

REV.
NO.

DESCRIPTION/ECO
NUMBER

APPV'D
DATE

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED
DATE

2/27/01

REVISION
DATE

REV.
NO.

SHEET
1 OF 1