







Max. Temperature: 260° during 10 seconds.


0955 329 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)
0955 329 3812 741	1	4-40 UNC		
0955 329 6811 741	2	M3		
0955 329 6812 741	2	4-40 UNC		
0955 329 7811 741	3	M3		
0955 329 7812 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	
 All Dimensions in mm Original Size DIN A 3	Techn. Character.			Free size tolerances
				D-Sub SMT, 25 poles Male, Straight with nuts and ground pads



Detail A



Direction of unreeling →



See TB 09 55 329 x81x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 329 3811 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 329 3812 741	1	4-40 UNC		
0955 329 6811 741	2	M3		
0955 329 6812 741	2	4-40 UNC		
0955 329 7811 741	3	M3		
0955 329 7812 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances			
				Dat.	Name	Scale	D-Sub SMT, 25 poles Male, Straight with nuts and ground pads		
			Detail.	25-Oct-11	Johnson.S				
			Insp.	17-Nov-11	Steven.W				
			Stand.	17-Nov-11	Steven.W				
			Zhuhai HARTING Limited 			TB 09 55 329 x81x		Page 2 / 2	
EC04070	17-Nov-11	Johnson.S				Sub.			
Mod.	Dat.	Name							