




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T	REV PER 0G3A-0561-01	08OCT02	—	JR/MS
	U	ECR-16-012830	07SEP2016	KR	MV



- 1 CIRCULAR MIL AREA RANGE: 275-325 MCM
- 2 TIN PL 0.00381[0.000150] MIN THK PER MIL-T-10727
- 3 SIGHT HOLE TO EXTEND APPROX TO CENTER OF BARREL APPLIES TO PART NUMBER 325803 ONLY



3 SIGHT HOLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 02/28/90	TE Connectivity			
DIMENSIONS: INCHES		CHK MS FEHER 23JAN95	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TL SHUTTER 23JAN95	PRODUCT SPEC			
0 PLC ± -		108-30200		APPLICATION SPEC		
1 PLC ± -		—		WEIGHT .158 LB		
2 PLC ± 0.51[0.020]		—		CUSTOMER DRAWING		
3 PLC ± -		—		SCALE 2:1		
4 PLC ± -		—		SHEET 1 of 1		
ANGLES ± -		—		REV U		
FINISH		—		RESTRICTED TO		
MATERIAL ANNEALED COPPER ASTM B-75		—		—		