






RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



备注:

1.材质:

1.1胶芯: LCP+30%G.F Black/Whiter/Colours

1.2端子: C2680-H, T=0.15mm; 镍底, 镀金1U"

1.3外壳: SUS201-1/2H, T=0.30mm; 整体镀镍

1.4中夹片: SUS301-1/2H, T=0.15mm

2.主要特性:

2.1额定电流: 3A

2.2接触阻抗: 40mΩ MAX

2.3绝缘阻抗: 100MΩ MIN 250V DC

2.4耐压测试: 100V AC

2.5沾锡性: 温度250±5℃, 时间5±0.5s

2.6整体插入力: 2.0kgf MAX

耐久前整体拔出力: 0.8kgf MIN

2.7使用寿命: 10000次

2.8工作温度: -30℃~+80℃



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X.' ±2' X.X' ±0.5'

UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

USB TYPE C 母座16P单排SMT 沉板2.1

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW524-USBC16-210B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2405281150

SHEET NO.

1 OF 1