





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
8628	6.0	.200	.630	7.92	1,000	C-2R
8632	28.0	.040	.340	4.27	2,800	C-2F



DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-1 1/4 STANDARD MIDGET FLANGE

DRAWN BY
L. WENGSTROM

APPV'D BY
J.K.

DATE
7/21/05

SIZE
A

FSCM NO.
55335

DRAWING
NO.

FLANGE T-1 1/4

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED
DATE

4/5/00

REVISION
DATE

7/21/05

REV.
NO.

B

SHEET

1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE
B	DELETE CANCELLED PART NO. 8646	7/21/05
A	LAMP DIA. TO 4.5 MAX.	4/21/00
	RELEASE & CANCEL 8637, 3585, 3518, 8551, DF09, DF737, DF329	4/5/00