





| JKL LAMP NUMBER | VOLTS RATED | AMPS $\pm 10\%$ | MSCP $\pm 25\%$ | LUMENS $\pm 25\%$ | AVERAGE LIFE HRS. | FILAMENT TYPE |
|-----------------|-------------|-----------------|-----------------|-------------------|-------------------|---------------|
| 266             | 2.5         | .350            | .200            | 2.51              | 20,000            | C-2R          |
| 253             | 2.5         | .350            | LENS            | END               | 20,000            | C-2R          |
| FG23            | 5.0         | .020            | .020            | 0.25              | 50,000            | C-2R          |
| 3152            | 5.0         | .060            | .150            | 1.89              | 5,000             | C-2R          |
| 7348            | 5.0         | .115            | .150            | 1.89              | 40,000            | C-2R          |
| 8705            | 6.0         | .040            | .030            | 0.38              | 10,000            | C-2V          |
| 337             | 6.0         | .200            | .630            | 7.92              | 1,000             | C-2R          |
| 7351            | 6.3         | .040            | .030            | 0.38              | 20,000            | C-2V          |
| 8708            | 6.3         | .075            | .230            | 2.89              | 1,000             | C-2R          |
| 379             | 6.3         | .200            | .400            | 5.03              | 50,000            | C-2F          |
| 398             | 6.3         | .200            | .550            | 6.91              | 5,000             | C-2R          |
| 709             | 10.0        | .014            | .004            | 0.05              | 50,000            | C-2F          |
| 397             | 10.0        | .040            | .080            | 1.01              | 30,000            | C-2F          |
| 7354            | 12.0        | .040            | .120            | 1.51              | 10,000            | C-2F          |
| 386             | 14.0        | .080            | .300            | 3.77              | 50,000            | C-2F          |
| 336             | 14.0        | .080            | .500            | 6.29              | 2,500             | C-2F          |
| 346             | 18.0        | .040            | .150            | 1.89              | 10,000            | C-2F          |
| 7355            | 28.0        | .040            | .200            | 2.51              | 50,000            | C-2F          |
| 388             | 28.0        | .040            | .300            | 3.77              | 25,000            | C-2F          |
| 334             | 28.0        | .040            | .340            | 4.27              | 4,000             | C-2F          |
| 7356            | 28.0        | .065            | .650            | 8.17              | 5,000             | C-2F          |

|                                                                                                                                |  |                                                                                                                       |  |                                                |                                |                                           |                        |
|--------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------|--|------------------------------------------------|--------------------------------|-------------------------------------------|------------------------|
| <b>METRIC</b><br><br>THIRD ANGLE PROJECTION |  | DIMENSIONS ARE IN MILLIMETERS<br>TOLERANCE UNLESS OTHERWISE SPECIFIED<br>1 PL +/- 0.2<br>2 PL +/- 0.20<br>ANGLE +/- 0 |  | <b>JKL COMPONENTS CORPORATION</b>              |                                |                                           |                        |
|                                                                                                                                |  |                                                                                                                       |  | TITLE<br><b>T-1 3/4 STANDARD MIDGET GROOVE</b> |                                |                                           |                        |
| DRAWN BY<br><b>L. WENGSTROM</b>                                                                                                |  | APPVD BY DATE<br><b>J.K. 8/2/05</b>                                                                                   |  | SIZE<br><b>A</b>                               | FSCM NO.<br><b>55335</b>       | DRAWING NO.<br><b>GROOVE BASE T-1 3/4</b> |                        |
| - CAD DRAWING -<br>MANUAL REVISIONS NOT PERMITTED                                                                              |  | SCALE<br><b>NONE</b>                                                                                                  |  | RELEASED DATE<br><b>10/11/00</b>               | REVISION DATE<br><b>8/2/05</b> | REV. NO.<br><b>A</b>                      | SHEET<br><b>1 OF 1</b> |

|          |                                                               |                     |
|----------|---------------------------------------------------------------|---------------------|
| REV. NO. | DESCRIPTION/ECO NUMBER                                        | APPVD DATE          |
| A        | DELETED PART #'S 393, 457, 276<br>RELEASE & CANCEL 7346, 7347 | 8/2/050<br>10/11/00 |