

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0		M1	REVISED PER ECO-11-004820	11MAR11	RK
						HMR

D

D

C



C

B



B

A

A




RECOMMENDED PANEL CUTOUT



RECOMMENDED HOLE PATTERN
1.57[.062] THICK PC BOARD
COMPONENT SIDE

- 1 2.54um[.000100] MIN TIN-LEAD FOR A MIN LENGTH OF .195 ON END OPPOSITE MATING FACE, OVER 1.27um[.000050] MIN NICKEL ON ENTIRE CONTACT.
- 2 2.54um[.000100] MIN TIN FOR A MIN LENGTH OF .195 ON END OPPOSITE MATING FACE, OVER 1.27 MIN NICKEL ON ENTIRE CONTACT.
- 3 HOUSING: NYLON, COLOR: SEE TABLE.
CONTACTS: BRASS

WHITE	3-213598-4
BLACK	3-213598-2
GRAY	3-213598-1
WHITE	213598-4
BLACK	213598-2
GRAY	213598-1
COLOR	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 23JUNE2005	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 23JUNE2005				
		APVD D. BOSSI 23JUNE2005	NAME			
		PRODUCT SPEC	RECEPTACLE ASSEMBLY, CONVENIENCE OUTLET			
MATERIAL		APPLICATION SPEC	-			
3		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=213598	RESTRICTED TO -
CONTACTS: 1		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 1	REV M1	