












Max. Temperature: 260° during 10 seconds.

0955 255 3611 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)			
0955 255 3612 741	1	4-40 UNC					
0955 255 6611 741	2	M3					
0955 255 6612 741	2	4-40 UNC					
0955 255 7611 741	3	M3					
0955 255 7612 741	3	4-40 UNC					
Part number	PL	Nut	Index designation				
 All Dimensions in mm Original Size DIN A 3			Techn. Character.		Free size tolerances		
				Dat.	Name	Scale 2 : 1	D-Sub SMT, 15 poles Female, Straight with nuts and ground pins
			Detail.	25-Oct-11	Johnson.S		
			Insp.	17-Nov-11	Steven.W		
			Stand.	17-Nov-11	Steven.W		
			Zhuhai HARTING Limited 			TB 09 55 255 x61x	
EC04070	17-Nov-11	Johnson.S				Sub.	
Mod.	Dat.	Name					




Detail A



Detail A

Direction of unreeling



See TB 09 55 255 x61x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 255 3611 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 255 3612 741	1	4-40 UNC		
0955 255 6611 741	2	M3		
0955 255 6612 741	2	4-40 UNC		
0955 255 7611 741	3	M3		
0955 255 7612 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances			
				Dat.	Name	Scale	D-Sub SMT, 15 poles Female, Straight with nuts and ground pins		
			Detail.	25-Oct-11	Johnson.S				
			Insp.	17-Nov-11	Steven.W				
			Stand.	17-Nov-11	Steven.W				
EC04070	17-Nov-11	Johnson.S	Zhuhai HARTING Limited				TB 09 55 255 x61x		Page 2 / 2
Mod.	Dat.	Name					Sub.		