

PIN CONNECTORS



BU-192120001



BU-192120003



BU-192120005

- Mueller offers three different pin connectors
- Vinyl insulated
- 3 AWG sizes
 - 12-10AWG (BU-192120001)
 - 16-14AWG (BU-192120005)
 - 22-18AWG (BU-192120003)
- Pin diameters
 - BU-192120001: .110in
 - BU-192120005: .074in
 - BU-192120003: .074in
- Quick connect style
- Max temperature rating of 75°C
- Voltage Rating: 600V
- All terminals are made of copper with tin plating
- Solid or stranded wire accepted
- Recommended strip length: ¼"
- All are UL listed