


© COPYRIGHT 1975 BY AMP
INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS
RESERVED. AMP INCORPORATED
PRODUCTS COVERED BY U.S. AND
FOREIGN PATENTS AND PATENTS
PENDING.

UNPUBLISHED AND NOT
REPRODUCED WITHOUT PERMISSION
OF AMP INCORPORATED

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED	P
D	REDESIGNED PER NPS 76-1627	6/22/77	AMH	1
A	REL -4 S2-20011	11/22/82	DKS	2
B	OBS -1 PER G-193	3/16/88	DKS	3
C	REACTIVATE PER G-5920	5/19/92	DKS	4
D	REACT PER 0720-0142-94	8/5/94	DKS	5
E	OBS -1 PER 0720-0964-96	6/96	DKS WTV	6
F	REV PER 063A-0561-01	10/02	DKS/MS	7



1/2	.515	54664-4
3/8	.390	54664-1
'Y'	'X'	PART NO

OBSOLETE

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .01$
ANGLES $\pm 5^\circ$

MATERIAL
COPPER
(ASTM B-75)

FINISH
TIN PLATE
(MIL-T-10727)

CONTRACT NO

DRI *W. D. Miller* 6/22/77CHK *W. D. Miller* 6/23/77

APPD

APPD *W. D. Miller* 6/23/77DSEN APPD *W. D. Miller* 6/23/77

OTHER APPD



AMP INCORPORATED
Harrisburg, Pa.

NAME

WIRE TERMINAL
AMPOWER - BENT 90°
WIRE SIZE - 4/C

SIZE

A

CODE IDENT NO

00779

DRAWING NO

54664

SCALE NTS

SHEET