

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010533

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Spring Terminal Insert, Female, 5-Pole, 16A, Silver (Ag) Plated Contacts, Size «34.2x14.6»

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	«34.2x14.6»
Component Type	Inserts - Spring Terminal
Insert Series	S-M16/5
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191830131
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Female
Insert Color	Grey
Material - Contact	Copper Alloy
Material - Insert	Polycarbonate
Material - Plating	Silver
Net Weight	16.280/g
Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	5
Stripping Length	9.00mm
Temperature Range - Operating	-40° to +125°C
Wire Size AWG	14-26
Wire Size mm²	0.14-2.50
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	400V
Material Info	
Engineering Number	7705.3360.0



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Mates With

936010534 Male Crimp Contact Insert

Use With

Series S-M Frames

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION