



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-770342	2007/07/16	Robert Hsu	Correct Pin Layout
D	LEN1390204	2013/09/02	Lu Di	Update Dimension
E	LEN1490285	2014/09/15	Vicky	Update Dimension




Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate : IP68
IP68: 1M of depth of water 24 hours
- * Do Mating Test After Glued
- * HD-SUB Conn.: PBT, Black Core
- * Plastic Jacket: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Ring: Silicone, Light Blue
- * Screw: Copper Alloy, Nickel Plated, #4-40 UNC
- * The 90° Board Lock Needs To Connect The Iron Shell
L 型支架需接鐵殼



Screw L=5.0 For Panel Thickness
Under 1.2mm
適用板厚 1.2mm 以下

Screw L=6.0 For Panel Thickness
Between 1.2~2.0mm
適用板厚 1.2~2.0mm 以下



Recommended Panel Cut-Out
建議挖孔尺寸

UNIT: mm		TITLE	HD26/M Conn., Panel, PCB 90° Add Board Lock
TOLERANCE		SCALE	1:1
.X ±0.25		SIZE	A4
.XX ±0.1		SHEET	1 OF 1
.XXX ±0.05		REV.	E
ANGLES ±1°		WC-REV.	A.3
			$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	HDB-26PMMP-SB8001	DRAWN BY	Vicky	DATE	2014-09-15
DWG NO.	HDB-26PMMP-SB8001	CHECKED BY	Sam	DATE	2014-09-15
CUSTOMER	ALTW	APPROVED BY	Rita	DATE	2014-09-15