


RECOMMAND PCB LAYOUT



SPECIFICATIONS


- Voltage rating: 250V AC, DC
- Current rating: 1A, AC, DC
- Withstanding voltage: 500V AC/minute
- Insulation resistance: 1000MΩ/min
- Temperature range: -40℃ - +105 ° C
- Contact resistance: 20mΩ max

WAFER

- Part No.: CS-1147R-02
- Poles: 2-16
- Material: LCP, UL94V-0
- Contact: Brass, Tin plated
- Q'TY: 1,000 pcs/bag
- STORAGE TEMPERATURE RANGE: +16℃ TO +26℃.
- RELATIVE HUMILITY: 45%~75%.

Poles	PART NO	DIMENSION (mm)	
		A	B
2	CS-1147R-02	1.25	4.25
3	CS-1147R-03	2.50	5.50
4	CS-1147R-04	3.75	6.75
5	CS-1147R-05	5.00	8.00
6	CS-1147R-06	6.25	9.25
7	CS-1147R-07	7.50	10.50
8	CS-1147R-08	8.75	11.75
9	CS-1147R-09	10.00	13.00
10	CS-1147R-10	11.25	14.25
11	CS-1147R-11	12.50	15.50
12	CS-1147R-12	13.75	16.75
13	CS-1147R-13	15.00	18.00
14	CS-1147R-14	16.25	19.25
15	CS-1147R-15	17.50	20.50
16	CS-1147R-16	18.75	21.75

RoHS 2.0



本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。													
类别	WAFER	品名	CS-1147R-02	X.	±0.50	材料		单位	mm	SHEET 1 OF 1			
版本	A/1	设计	李文物	X.X	±0.30	颜色		比例	1:1		修改内容	修改日期	
制定部门	工程课	绘制	李文物	X.XX	±0.20	画法		数量			加储存方式	2017-08-10	
工程图号	CST-1147R	审核	姚培柱	X.XXX	±0.10								
制定日期	2022-02-23	核准	周中湖	X.XXXX	±0.05	 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.							

本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利.