






RoHs



CIRCUIT DIAGRAM



The Main Thchnology Performance

|                      |              |
|----------------------|--------------|
| Rate voltage,current | 50mA DC12V   |
| Contact resistance   | ≤100mΩ       |
| Operating force      | ±50gf        |
| Travel               | 0.20±0.10mm  |
| Insulated resistance | ≥100MΩ       |
| Dielectric strength  | ≥250VAC/1min |

TS50310-411-AA

按力码 按力可定制

100=10

150=15

280=28

高度码

H3. 5=035

PCB.WELDING DRAWING

GENERAL TOLERANCES  
UNLESS SPECIFIED

|      |       |       |     |
|------|-------|-------|-----|
| X.X  | ±0.35 | X.°   | ±5° |
| .XX  | ±0.25 | X.X°  | ±3° |
| .XXX | ±0.15 | X.XX° | ±1° |

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.

TS50310-411-AA

TITLE:

3x6 SMD TACT SWITCH

DESIGN:

James

CHED:

Talen

APPD:

Sophia

CUSTOMER

SIZE

UNITS

A4 MM

SCALE

SHEET

N:A 1/1