






RoHs


VER	MARK	PR. BY	DESCRIPTION	DATE




← E
← D
← C
← B
← A



CIRCUIT DIAGRAM



E	按钮	PPA	1	白/黑色
D	盖板	黄铜	1	镀银
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	白/黑色
A	卡件	黄铜	1	镀银
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR



The Main Thchnology Performance


Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±50gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min

TS5021C-411-AA

按力码 按力可定制
100=10
150=15
280=28

高度码
H3.5=035

PCB.WELDING DRAWING

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.35	X.° ±5°	PART NO.	TITLE:	
.XX ±0.25	X.X° ±3°	TS5021C-411-AA	3x6 SMD TACT SWITCH	
.XXX ±0.15	X.XX° ±1°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
			N:A	1/1