




RoHs



PCB.WELDING DRAWING

The Main Thchnology Performance

Rate voltage.current	50mA DC12V
Contact resistance	$\leq 100\text{m}\Omega$
Operating force	$\pm 50\text{gf}$
Travel	$0.25\pm 0.10\text{mm}$
Insulated resistance	$\geq 100\text{M}\Omega$
Dielectric strength	$\geq 250\text{VAC}/1\text{min}$


TS80220-413-AA

- 按力码 按力可定制

100=10
150=15
280=28

-高度码
H4. 3=043
H4. 5=045
H4. 8=048
H5. 0=050
H5. 5=055
...
H10. 0=100

<i>E</i>	按钮	PPA	1	黑色
<i>D</i>	盖板	铁盖板	1	镀铜锡
<i>C</i>	弹片	不锈钢	1	镀银
<i>B</i>	本体	PPA	1	黑色
<i>A</i>	卡件	黄铜	1	镀银
<i>ITEM</i>	<i>DESCRIPTION</i>	<i>MATERIAL</i>	<i>QTY</i>	<i>FINSH/COLOR</i>

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd HMTCONN			
X.X ±0.35	X.° ±5°	PART NO.		TITLE:	
.XX ±0.25	X.X° ±3°	TS80220-413-AA		6x6 DIP TACT SWITCH	
.XXX ±0.15	X.XX° ±1°	DESIGN:	James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED:	Talen		UNITS
		APPD:	Sophia		MM
				SCALE	SHEET
				N:A	1/1