

<i>VER</i>	<i>MARK</i>	<i>PR. BY</i>	<i>DESCRIPTTON</i>	<i>DATE</i>

Specification:






1. Electrical Characteristics:
 - Contact Current Rating: 0.5 Amperes.
 - Dielectric Withstanding Voltage: AC 500V r.m.s.
 - Insulation Resistance: 1000 MΩ Minimum.
 - Contact Resistance: 40 mΩ Maximum.
2. Environmental:
 - Operating Temperature: -25°C ~ +90°C.
3. Environmental:
 - Mating Cycles: 5,000 Insertions.
4. Mechanical Characteristics:
 - Card Push Insertion/Out Force: 0.2 ~ 1.40 kgf.
 - Contact Separation Force: 0.20 kgf Minimum.
5. Material:
 - Insulator: HI-Temp Plastic UL 94V-0 Rated.
 - Contact: Copper Alloy (t=0.15mm).
 - Shell: Stainless Steel (t=0.15mm).
 - Spring: SWP.

PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)


Circuit Diagram for Detect Switch

WITHOUT CARD	OPEN	CD GND(SHE)
INSERTING CARD	CLOSE	CD GND(SHE)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd.	
.X ±0.35	.X° ±3°	PART NO. TF1011C-9P311-H200	TITLE: MICRO SD CARD PUSH PUSH SMT 镀金 外焊
.XX ±0.25	.XX° ±2°		
.XXX ±0.15		DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	SCALE N:A
			UNITS MM
			SHEET 1/2



 PAD AREA
 KEEP OUT AREA
 RECOMMENDED PCB LAYOUT
 GENERAL TOLERANCE ± 0.05




1. 材质要求:

- 1.1 纸箱的材质为K=K;外形尺寸为34*34*38.5;
- 1.2 卷盘的材质为PS,卷盘的外形尺寸为 $\phi 330*30.4$;
- 1.3 卷带的材质为PS,卷带的外形尺寸为20200*24.00*3.0mm;

2. 包装方式:

- 2.1 将卷带放入包装机后,前空5PCS,后放产品1000PCS,再后空5PCS;上带留300MM长度。
- 2.2 将包装好的产品从包装机上取下并包装好,贴上内盘标签;
- 2.3 把累叠好的12盘叠放入纸箱中共计12Kset,上下放纸板,纸箱四个角塞护角纸;
- 2.4 把包装好的成品打包封箱,并在纸箱外贴上标签

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
.X ±0.35	.X° ±3°	PART NO. TF1011C-9P311-H200	TITLE: MICRO SD CARD PUSH PUSH SMT 镀金 外焊	
.XX ±0.25	.XX° ±2°			
.XXX ±0.15		DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		MM
				SCALE
				SHEET
				N:A
				2/2