




RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE

CIRCUIT DIAGRAM

PCB.WELDING DRAWING

The Main Thchnology Performance

Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±50gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min

TS40110-411-AA

按力码 100=10 150=15 280=28 按力可定制

高度码 H2. 5=025

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.35	X.° ±5°	PART NO. TS40110-411-AA	TITLE: 4.2*3.2*2.5 SMD TACT SWITCH
.XX ±0.25	X.X° ±3°	DESIGN: James	CUSTOMER
.XXX ±0.15	X.XX° ±1°	CHED: Talen	SIZE A4
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1