




REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

- 规格说明:Specifications:
- 电气特性:Electrical:
- 1.额定电流: Current Rating
1.5A/contact terminal
 - 2.额定电压: Voltage Rating
30V DC
 - 3.接触电阻:Contact Resistance
30 milliohms MAX
 - 4.耐压:Dielectnc Withstanding Voitage:
500 V AC AT Sea Levol
 - 5.绝缘电阻:Lnsulation Resistance:
1000MEGA ohms MIN
- 物理性能:Mechanical:
- 1.插拔力: Connector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
 - 2.端子保持力: Terminal Retenion
1.0kgf(MIN)
- 原材料:Matorial:
- 1.塑胶:Housing:
Hing Temperature Tnermaplastics,
 - 2.端子:Contact:Copper Alloy C2680
 - 3.外壳:Shell: Copper Alloy C2680/SPCC
- 电镀:Finish:
- 1.端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls
 - 2.外壳:Shell:
铜壳四周镀80U”(MIN)锡
镀金区域镀100-200U”镀金1U”
Nickel Plating

DIMENSION CLASSIFICATION			台灣碩方精密電子科技有限公司							
■ : CRITICAL			TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD							
☒ : MAJOR			TITLE		USB-100D-L257 插件卧式短体USB连接器			開關, 連接器 SOFNG		
TOLERANCE TABLE										
.X	±	0.40	PART NO.	SOF-G006			SERIES	SD106		
.XX	±	0.25	APPROVED	Peck	DWG NO.		SOF-10USB			
.XXX	±	0.10	CHECKED	Paul	SCALE	1:1	UNIT	mm	SIZE	A4
ANGLE	±	2°	DRAWIN	David			REV	AO	SHEET NO.	1/1