






RoHs


VER	MARK	PR. BY	DESCRIPTION	DATE



CIRCUIT DIAGRAM



PCB.WELDING DRAWING



The Main Thchnology Performance


Rate voltage,current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±50gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min

TS5041C-411-AA

按力码 按力可定制
100=10
150=15
280=28

高度码
H4.3=043
H4.5=045
H5.0=050

E	按钮	PPA	1	白/黑色
D	盖板	铁盖板	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	白/黑色
A	卡件	黄铜	1	镀银
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.X ±0.35	X.° ±5°	PART NO. TS5041C-411-AA	TITLE: 3x6 SMD TACT SWITCH		
.XX ±0.25	X.X° ±3°				
.XXX ±0.15	X.XX° ±1°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1