







RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



CIRCUIT DIAGRAM



PCB.WELDING DRAWING

TS80510-411-AA

The Main Thchnology Performance

Rate voltage.current	50mA DC12V
Contact resistance	≤100mΩ
Operating force	±50gf
Travel	0.20±0.10mm
Insulated resistance	≥100MΩ
Dielectric strength	≥250VAC/1min

按力码 按力可定制

100=10
150=15
280=28

高度码

H4. 3=043
H4. 5=045
H4. 8=048
H5. 0=050
H5. 5=055

...
H18. 0=180

E	按钮	PPA	1	黑色
D	盖板	铁盖板	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.35	X.°	±5°
.XX	±0.25	X.X°	±3°
.XXX	±0.15	X.XX°	±1°

MANUFACTURE DWG



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
TS80510-411-AA

TITLE:
6x6 SMD TACT SWITCH

DESIGN: James
CHED: Talen
APPD: Sophia

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1