



Specifications:
 规格:
 Voltage rating:300VAC/DC
 额定电压: 300V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: ≥1000V AC/分钟
 Temperature range:-55°C~+85°C
 温度范围: -55°C~+85°C
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:20mΩMax
 接触电阻: ≥20mΩ
 Material:
 材质:
 The main body:PBT UL 94V-0
 主体: PBT UL 94-0
 The shell:Rian, Nicke plating/Tin plating
 外壳: 铁、镀镍/锡
 Terminal:Brass plating material no.
 端子: 黄铜、电镀见料号
 The rive: copper alloy #4-40UNC tin plating
 铆钉: 铜合金、#4-40UNC 镀锡

X02 XX F X X X 5 H
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series NO.
- ② Row No.Pin No.XX-09:15;25;37
- ③ Welding Board Angle :F-Fmale
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:7:5AuSn
- ⑥ B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 5:Front lock screw after riveting
- ⑧ H:heighten

NO.of Contolt	A±0.25	B±0.15	C±0.38	D±0.25	E±0.25
9	16.33	24.99	30.81	19.28	11.8
15	24.66	33.32	39.14	27.51	19.39
25	38.78	47.02	53.04	41.28	33.24
37	54.84	63.50	69.32	57.71	49.86

广东星坤科技股份有限公司
 文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE:	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm/in	DWG NO.:	
APPD		DATE		SIZE: A4	X02XXFXXX5H	
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0