

A
B
C


1

2






3

4

5



SECTION A-A



材料及电镀
①.塑件主体: PA66, UL94V-0
②.焊 针: 黄铜, 镀镍

电气性能
额定电压: 300V
额定电流: 10~15A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ \DC500V
耐 电 压: AC2000V\1Min

机械性能
温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ ,5秒

Circuits	Product name	Dimensino(mm)	
		A	B
2	2EDG-5.08-2A	5.08	11.76
3	2EDG-5.08-3A	10.16	16.84
4	2EDG-5.08-4A	15.24	21.92
5	2EDG-5.08-5A	20.32	27.00
6	2EDG-5.08-6A	25.40	32.08
7	2EDG-5.08-7A	30.48	37.16
8	2EDG-5.08-8A	35.56	42.24
9	2EDG-5.08-9A	40.64	47.32
10	2EDG-5.08-10A	45.72	52.40
11	2EDG-5.08-11A	50.80	57.48
12	2EDG-5.08-12A	55.88	62.56
13	2EDG-5.08-13A	60.96	67.64
14	2EDG-5.08-14A	66.04	72.72
15	2EDG-5.08-15A	71.12	77.80
~	~	~	~
24	2EDG-5.08-24A	116.84	123.52

			GENERL TOLERANCE	制 图 DRAWING	ZHE JIANG DELI CONNECTORS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X.X ±0.50	批 准 APPROVAL	产品名称 TITLE	2EDG-5.08-A	版 本 REV.	A
1	初版发行		X.XX ±0.30	比 例 SCALE	产品料号 PART NO.		单 位 UNITS	mm
			X.XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°					