





TABLE-1					
NO. OF CONTACTS	DIM.	A ± 0.5	B ± 0.25	C ± 0.3	D ± 0.3
2		5.5	2.5	2	1.5
3		8	5	3	2
4		10.5	7.5	4	2.5
5		13	10	5	3
6		15.5	12.5	6	3.5
7		18	15	6	6
8		20.5	17.5	6	8.5
9		23	20	6	11
10		25.5	22.5	6	13.5

HOW TO ORDER

IL-**-P-S3EN2-*(N)

NEW TYPE (5-CONTACT ONLY)
INSULATOR COLOR (STANDARD COLOR;
LIGHT BROWN ISN'T SHOWN)
THICKNESS OF APPLICABLE P.C BOARD
(2;1.6~2.4 THICK)

INSULATOR TYPE
CONTACT TYPE
CONTACT SPACING (25mm ONLY)
CONTACT ROW (SINGLE ONLY)
POST SIDE
NO. OF CONTACTS (SEE TABLE 1)
SERIES PREFIX

2	INSULATOR	1	THERMOPLASTIC		
1	CONTACT	SEE: TABLE 1	COPPER ALLOY	TIN OVER NICKEL	
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	PART NO.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON: FRACTIONS DECIMALS ANGLES ± 0.8 ± 0.5 ± 0.2		DATE DEC. 1977 DRAWN E. MURANO CHECKED H. Takeda APP'D T. SOMBI APP'D Joe Samito	TITLE JAE-CONNECTOR.COM STRIGHT PIN HEADER IL-**-P-S3EN2-*		IND. CO., LTD. FACTORY NAKAGAMI-CHO, AKISHIMA -SHI TOKYO. JAPAN
TREATMENT OR FINISH		3rd Angle Drawing	SCALE x 4	DWG. SIZE B	WT.
NEXT ASS'Y USED ON NEXT ASS'Y FINAL ASS'Y APPLICATION QT'Y REQ'D		DWG. NO. SJ015093-E		SHEET 1 OF 1	