





CIRCUIT DIAGRAM




PCB. WELDING DRAWING

Specification

Operating Life	100, 000					
Contact rating	50mA@12V DC.	F	button	LCP	1	Black
Insulation resistance	100MΩ min.	E	Cover	Stainless steel	1	cleaning
Contact resistance	100mΩ max. initial	D	Dust proof adhesive	Polyimide	1	Orange yellow
Dielectric Strength	250 V AC(1mn)	C	shrapnel	Stainless steel	2	Silver plated
Travel	0.2±0.1mm	B	ontology	LCP	1	Black
Storage Temperature	- 30° C to 70° C	A	Card	Phosphor copper	1	Silver plated
		ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR OR

Type	Operating Force (gf)	Height mm	Button Shape (6, J, T)	Leads (6, J, T)	Ground pin (0, 1)	Pegs Option (0, 1)
YTS1T011	2 200G±50	C 2.5000	YTS1T011	J	0	1
	1 180gf±50	B 2.0000				
		A 1.8000				

X. ±0.50	X.° ± 2°	UNITS mm	PART NO. YTS1T011	TITLE: TACTILE SWITCH 3x4两脚翘脚带柱
.X ±0.30	.X° ± 1°			
.XX ±0.10	.XX° ± 0.5°	MAT'L	APPD: ROGER	DWG NO. : YTS1T011
.XXX ±0.05		FINISH		
THESE DRAWINGS SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANYMANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD Email at info@yiyuanswitches.com			CHKD: ROC	
			DR: BILLY WANG 2020/08/21	
				SCALE 1/1
				SHEET 1/1
				REV. A1