




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B1	REVISED PER ECO-09-021480	08OCT2009	CR	DG
			B2	REVISED PER ECO-10-016367	02AUG2010	JY	SY



1888861-2 AND 1888861-9
SHOWN WITHOUT PICK AND PLACE DEVICE



1888861-4 AND 1-1888861-0
SHOWN WITHOUT PICK AND PLACE DEVICE



1888861-8 AND 1-1888861-2
SHOWN WITHOUT PICK AND PLACE DEVICE

△ MATERIAL: LCP, BLACK.

△ MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.

△ FINISH: 0.76um MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03um MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81um MIN NICKEL PLATE PER QQ-N-290.


△ MATERIAL: NICKEL-SILVER PER ASTM B 122.

△ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.

6. REFER TO CUSTOMER DRAWING 1761987 FOR CONNECTOR DETAILS.

7. PACKAGED IN TAPE AND REEL PER EIA-481.




△ FINISH: 0.38um MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03um MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81um MIN NICKEL PLATE PER QQ-N-290.



1888861-6 AND 1-1888861-1
SHOWN WITHOUT PICK AND PLACE DEVICE


△	THRU HOLE	3.5	17.8	16	16	36	18.05	36	1-1888861-2
		2.8	17.8	16	16	36	18.05	36	1-1888861-1
	PRESS FIT	-	17.8	16	16	36	18.05	36	1-1888861-0
△	THRU HOLE	2	17.8	16	16	36	18.05	36	1888861-9
		3.5	17.8	16	16	36	18.05	36	1888861-8
	PRESS FIT	-	17.8	16	16	36	18.05	36	1888861-6
△	THRU HOLE	2	17.8	16	16	36	18.05	36	1888861-4
		2	17.8	16	16	36	18.05	36	1888861-2
FINISH	REMARKS	G	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS THE USER'S RESPONSIBILITY TO OBTAIN THE LATEST REVISIONS OF THIS DRAWING. NO PARTS OR SERVICES SHOULD BE ORDERED OR PROVIDED FOR THIS DRAWING WITHOUT THE LATEST REVISIONS.		DWN B. MCMASTER 21FEB07	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK D. GORENC 21FEB07	NAME EVERCLEAR Mini-SAS RIGHT ANGLE, INTERNAL RECEPTACLE ASSEMBLY, WITH UNKEYED SHELL	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		APVD D. GORENC 21FEB07	SIZE A100779C=1888861	
MATERIAL SEE NOTES		PRODUCT SPEC 108-2234	RESTRICTED TO	
CUSTOMER DRAWING		APPLICATION SPEC -	SCALE 8:1	
		WEIGHT -	SHEET 1 OF 3	
			REV B2	



$$-Z-$$

1888861-2
PICK AND PLACE DEVICE OMITTED FOR CLARITY



1888861-4
SAME AS 1888861-2 EXPECT AS SHOWN

AMP 4805 REV 31MAR2000

