

0669	0670	0673	0666									
0669-0-15-XX-30-XX-10-0 Solder mount in .060 min. mounting hole	0670-0-15-XX-30-XX-10-0 Solder mount in .060 min. mounting hole	0673-0-15-XX-30-XX-10-0 Surface Mount	0666-0-15-XX-32-XX-10-0 Solder mount in .064 min. mounting hole									
0341	0252	0678	0676									
0341-0-15-XX-30-XX-10-0 Press-fit in .073 mounting hole	0252-0-15-XX-32-XX-10-0 Hex press-fit in .057 plated thru hole	0678-0-15-XX-32-XX-10-0 Press-fit in .057 mounting hole	0676-0-15-XX-30-XX-10-0 Press-fit in .057 mounting hole									
0697	0668	0253/1033										
			<table><tr><th>Basic Part Number</th><th>Length L</th><th>Depth N</th></tr><tr><td>0253-0</td><td>.173</td><td>.148</td></tr><tr><td>1033-0</td><td>.203</td><td>.162</td></tr></table>	Basic Part Number	Length L	Depth N	0253-0	.173	.148	1033-0	.203	.162
Basic Part Number	Length L	Depth N										
0253-0	.173	.148										
1033-0	.203	.162										
0697-0-15-XX-30-XX-10-0 Press-fit in .057 mounting hole	0668-0-15-XX-30-XX-10-0 Press-fit in .057 mounting hole	XXX3-0-15-XX-30-XX-10-0 Press-fit in .057 mounting hole										
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2° ORDER CODE: <u>XXXX</u> - 0 - 15 - <u>XX</u> - <u>3X</u> - <u>XX</u> - 10 - 0 BASIC PART # SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 15 10μ" GOLD OVER NICKEL SPECIFY CONTACT FINISH: 02 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL SELECT CONTACT #30 or #32 CONTACT (DATA ON PAGE 208)												