






Performance:

1. Rated Current: 2.0 A
2. Rated Voltage: 12 V
3. Withstand Voltage: 500 V
4. Contact Resistance: 30 m Ω
5. Insulation Resistance: 500 M Ω
6. Operating Temperature: -40° C to +85° C
7. Plastic Parts (Material): LCP
8. Contact Points (Material): Phosphor Bronze,
with gold plating of 3U" on the contacts
9. Service Life: More than 3,000 times


A. Series: 04:15 Series
B. Spring contact pitch: F-2.54mm
C. Fixing method: 4-90° SMT
D. Product height: 1-H3.8
E. PIN NO: 2-2P(2-6PIN)
F: Main body material: 0-LCP
G: Spring contact material: 0-Phosphor Bronze Gold Plated
H: Mold code: 0-Convention

TITLE:	
2. 54mm H3.8 X-PIN 卧贴带柱	
DWG NO: 04F41-P036	
PART NO: 04F4100.31	
MODEL NO: 04F41-*-000	
	NAME:
	DC CONN



			GENERAL TOLERANCE	
			$\geq 0 \sim 2 <$	± 0.15
DESIGN	WANGGUIFA	2018.06.12	$\geq 2 \sim 5 <$	± 0.25
CHECKED	ZHENGUILAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
APPROVED	LILIANJIANG	2018.06.14	≥ 5	± 0.35

FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.

WWW.KKK-JP.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer