



## 1030 ⇒ 1032



**103X-X-05-XX-00-00-01-0**  
Press-fit in .057 mounting hole


| Basic Part Number | # of Wraps | Wrapost Length A |
|-------------------|------------|------------------|
| 1032-1            | 1          | .260             |
| 1031-2            | 2          | .360             |
| 1030-3            | 3          | .500             |

## 1216




**1216-0-05-XX-00-00-01-0**  
Press-fit in .056 mounting hole

## 1095




**1095-0-05-XX-00-00-01-0**  
Swage mount in .094 hole  
For .062 thick board

## 1214




**1214-0-05-XX-00-00-01-0**  
Press-fit in .059 mounting hole

## 1212




**1212-0-05-XX-00-00-01-0**  
Press-fit in .061 mounting hole

## 1213




**1213-0-05-XX-00-00-01-0**  
Press-fit in .061 mounting hole

## 0318




**0318-3-05-XX-00-00-01-0**  
Press-fit in .057 mounting hole

## 1302



**1302-0-05-XX-00-00-01-0**  
Press-fit in .057 mounting hole

## 1097



**1097-0-05-XX-00-00-01-0**  
Swage mount in .094 hole  
for .062 thick board

### SPECIFICATIONS

**PIN MATERIAL:**  
Brass Alloy 360, 1/2 Hard  
Swage pins are annealed

**DIMENSION IN INCHES**  
**TOLERANCES ON:**  
LENGTHS: ±.005  
DIAMETERS: ±.002  
ANGLES: ± 2°

**ORDER CODE: XXXX - X - 05 - XX - 00 - 00 - 01 - 0**

**BASIC PART #**

**SPECIFY PIN FINISH:**

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)
- ◇ 21 20μ" GOLD OVER NICKEL (RoHS)

