





SIGN	DATE	DESCRIPTION	APPROVER
△	04/22`08	pin尖改為球面。	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



SECTION A-A

Material

- Item① Terminal (Body): Thermoplastic (UL94V-0)
- Item② Male contact pin: Brass,Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 15A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

KG xx 00 x 0 xxxx G

- 02 2 CONTACTS 0 Black (RAL9005) 0000:standard Pb < 40,000ppm
03 3 CONTACTS 2 Red (RAL3001/D) Any special item by (RoHS)
... ... 3 Orange(RAL2011/P) customer request,
24 24 CONTACTS 4 Yellow(RAL1018/A) please contact sales
5 Green(RAL6018/T) department.
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

Poles	2	3	4	5	6	7	8	9	10	11	12	13
Dim A	7.80	12.80	17.80	22.80	27.80	32.80	37.80	42.80	47.80	52.80	57.80	62.80
Dim B	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00
Dim C	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL	±0.15					±0.20						
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	67.80	72.80	77.80	82.80	87.80	92.80	97.80	102.80	107.80	112.80	117.80	
Dim B	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00	
Dim C	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00	
TOL	±0.30					0.40						

ANYTEK					CUSTOMER COPY				
					ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD				
TITLE	KG 5.0								
PART NO.	KGxx00x0xxxxG				DWG NO.	8KG0001			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Tason 09/17`07	Tason 09/17`07			UNIT: mm		X.	±0.5
						SCALE: NONE		X.X	±0.3
								X.XX	±0.1
				SHEET: 01/01		REV.: C		X°	±1°