













THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC. IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION. CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX3INSMSC


MALE INSULATOR, SOLDER CONTACT

CONTACT LAYOUT	03	04	07
FRONT SIDE VIEW			
REAR SIDE VIEW			
CONTACT			
ISO VIEW			
CONTACT	ØC	2	1.6
	ØF	1.9	1.5
	MAX. AWG	16	18
	MAX. CURRENT RATING (A)	30	17
	CONTACT RESISTANCE (mΩ)	2.5	2.5
INSULATOR	NUMBER OF CAVITY	3	7
	MAX. CURRENT RATING	25	15
	TEST VOLTAGE (Vrms)	3600	2200
	WORKING VOLTAGE (Vdc/Vrms)	1600/1200	1100/830



CONTACT TYPE : M (MALE)
CONTACT TERMINATION : S (SOLDER)
MATERIAL :
CONTACT: BRASS
CLIP: COPPER ALLOY
INSULATOR: PEEK
FINISH:
CONTACTS: GOLD

CATALOG NUMBER DESCRIPTION



B	RELEASED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	SKV 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE
JBX, SIZE 3, MALE INSULATOR, SOLDER CONTACT

CAT NO.
JBX3INSMS

CAGE NO: 09922SIZE: B

CUSTOMER

INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.

WWW.SOURIAU.COM

APPROVAL

DRAWN: SKV02-02-15
CHKD : EV02-02-15
DSGN : EV02-02-15
MFG : DH02-02-15
QC : BB02-02-15

DRAWING SCALE: NA

DRAWING NO. REV

JBX3INSMSCB

1 OF 2

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99

These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited


LINEAR MEASURE:

mm

INCH

mm (INCH)

THIRD ANGLE PROJECTION



TOLERANCES UNLESS OTHERWISE SPECIFIED

No. OF PLACES	mm [INCH]
ONE PLACE	±3 [±.1]
TWO PLACES	±0.5 [±.02]
THREE PLACES	±0.25 [±.010]

ANGLES±1°

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX3INSMSC

CONTACT LAYOUT		08	10	14	18	22	30
FRONT SIDE VIEW							
CONTACT							
ISO VIEW							
CONTACT	ØC	1.3	1.3	0.9	0.9	0.7	0.7
	ØF	1.1	1.1	0.8	0.8	0.81	0.81
	MAX. AWG	20	20	24	24	22	22
	MAX. CURRENT RATING (A)	15	15	10	10	7	7
INSULATOR	CONTACT RESISTANCE (mΩ)	3	3	3.5	3.5	5	5
	NUMBER OF CAVITY	8	10	14	18	22	30
	MAX. CURRENT RATING	12	12	9	7	5.5	3.5
	TEST VOLTAGE (Vrms)	2000	1400	1700	1400	1200	800
	WORKING VOLTAGE (Vdc/Vrms)	830/560	600/420	830/560	660/460	560/400	400/260

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES±1°			

DRAWING TITLE					
JBX, SIZE 3, MALE INSULATOR, SOLDER CONTACT					
CAT NO.					
JBX3INSMS					
CAGE NO: 09922		SIZE: B			
CUSTOMER		SOURIAU	APPROVAL	DRAWN: SKV	02-02-15
				CHKD : EV	02-02-15
				DSGN : EV	02-02-15
				MFG : DH	02-02-15
				QC : BB	02-02-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		WWW.SOURIAU.COM	DRAWING SCALE: NA		
			DRAWING NO.		
			JBX3INSMSC		
			B		
				2 OF 2	