

1234567891011

技术参数 (SPECIFICATION):

温度范围 (TEMPERATURE RANGE): -40~+70℃

额定电压 (VOLTAGE RATING): 125V

额定电流 (CURRENT RATING): 1.5A

接触电阻 (CONTACT RESISTANCE): $\leq 30m\Omega$

绝缘电阻 (INSULATION RESISTANCE): $\geq 500M\Omega$

耐压 (DIELECTRIC STRENGTH): 500V AC/(50HZ)/Min

插拔力 (MATING AND UNMATING FORCE): 3~20N

寿命 (DURABILITY): 750 CYCLES MIN

Table 1

X	Terminal Plating
0	Au Fu" Plating
1	Au 1u" Plating
2	Au 2u" Plating
3	Au 3u" Plating
4	Au 6u" Plating
5	Au 10u" Plating
6	Au 15u" Plating
7	Au 30u" Plating

Material & Plating

Part NO.:

RCH5210-YE-X-XX

Material & Color





Table 2

XX	Material/Color
BB	PBT/BLACK
BW	PBT/WHITE
AB	PA/BLACK
AW	PA/WHITE
OO	OTHER/OTHER

2	插针	PHOSPHOR BRONZE	8	"FU"	
1	塑座	PBT	1	BLACK	
序号	名称	材料	数量	镀层/颜色	备注

 温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

一般公差		品名:	RCH-52-10(有耳)		
30~	± 0.25	料号:	RC01222		
10~20	± 0.20	型号:	RJ45	图号:	
~10	± 0.15	版本:	单位:mm	比例: 1:1	纸张: A4
角度:	$\pm 2^\circ$	页码:	1 of 1		



PCB LAYOUT
(TOP VIEW)

网络插座外形图

绘图:		日期:	
审核:		日期:	
核准:		日期:	

A/O 新出版发行

版次 变更履历

变更单号 绘制 日期 核准

该图面供温州瑞川电子有限公司内部使用, 不得私自复印