

## Coaxial Panel Connector 22\_BNC-50-0-5/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0074 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00010863
Catalogue drawing	DCA-00010865
Mounting hole	DOU-00008762

### Ordering Information

Bulk 100 pcs package	22_BNC-50-0-5/133_NH
Single package	22_BNC-50-0-5/133_NE