



0489



Basic Part Number	Length A
0489-0	.102
0489-1	.199
0489-2	.299


0489-X-15-XX-11-XX-04-0
Press-fit in .041 mounting hole.

0463




0463-0-15-XX-21-XX-04-0
Press-fit in .043 mounting hole.
shell is Phos. Br. Alloy 544 (B2)

0466




0466-0-15-XX-21-XX-04-0
Press-fit in .043 mounting hole.
shell is Phos. Br. Alloy 544 (B2)

7491




7491-0-15-XX-X1-XX-04-0
Press-fit in .042 mounting hole

0462




0462-0-15-XX-X1-XX-04-0
Press-fit in .043 mounting hole

0560




0560-0-15-XX-11-XX-10-0
Hex press-fit in .043 plated thru hole

5557



5557-0-19-XX-21-XX-10-0
Wire termination and Press-fit in .043 hole

5552



5552-0-15-XX-05-XX-10-0
Solder mount in .040 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#05, #11 or #21 CONTACT (DATA ON PAGES 206 & 207)