




PART NO.	Packing reel	QTY
20279-001E-01	Corrugated paper reel	2500
20279-001E-02	Plastic reel	2500
20279-001E-03	Plastic reel	5000



RECOMMENDED FOOTPRINT PATTERN



Notes.

1. Material
 - (1) Housing : LCP, UL94V-0, white
 - (2) Contact : brass
 - Au 0.1 μ m MIN. over Ni 1.27 μ m MIN.
 - (3) Ground Contact : phosphor bronze
 - Au 0.05 μ m MIN. over Ni 1.27 μ m MIN.
 2. Coplanarity : 0.1mm MAX.
 3. Packing : emboss tape
 4. Mating partner Part No. :
 - 20278-***R-***
 - 20351-***R-***
 - 20311-***R-***
5. This is "Pb-free" connector.
6. RoHS compliant. DC0-7.2GHz


Notes.

1. 材料
 - (1) ハウジング : LCP, UL94V-0, 白色
 - (2) コタ外 : 黄銅
 - 金メッキ 0.1 μ m MIN. 下地 ニッケルメッキ 1.27 μ m MIN.
 - (3) クラフト コタ外 : リン青銅
 - 金メッキ 0.05 μ m MIN. 下地 ニッケルメッキ 1.27 μ m MIN.
 2. コプラナリテ : 0.1mm MAX.
 3. 梱包 : エンボステープ
 4. 嵌合相手 Part No. :
 - 20278-***R-***
 - 20351-***R-***
 - 20311-***R-***
5. 本コタ外は "Pb-free" である
6. RoHS指令を満足している


MATING

Plug P/N 20278-***R-***
20351-***R-37

4 $\pm$ 0.4 at 20278-***R-08, 13, 32
4.7 $\pm$ 0.4 at 20278-***R-18
4.7 $\pm$ 0.4 at 20351-***R-37



Plug P/N 20311-***R-***



I-PEX DAICHI SEIKO CO.,LTD.
I-Pex Business Company

TITLE
MHF series micro coaxial
connector receptacle vertical

14	Z12046	H.M.	20n./20/12	FK	DESIGN BY	DATE	I-PEX IDA-ICHI SEIKO CO.,LTD. I-Pex Business Company	TITLE MHF series micro coaxial connector replaceable vertical	SCALE	UNIT	DWG. No.	SHEET	REV.
13	Z10262	H.M.	Jun./08/11	E.K.	K.Obayashi	Jun./07/01							
12	Z11032	Y.H.	Jan./28/11	E.K.	CHKD BY	DATE							
11	Z11030	H.M.	Jan./26/11	E.K.	E.Kawabe	Jun./07/01							
10	Z10101	Y.H.	Mar./08/10	E.K.	APPD BY	DATE							
REV	ECN	BY	DATE	APP	K.Katabuchi	Jun./07/01							
SERIES No.	REV/RECORD	R7			CUSTOMER COPY	PROJECTION			10:1	mm	20279	1/1	14