

# Actuator

92-  
343.400



<https://eao.com/p/92-343.400>

Your product:

---



## 92-343.400 Actuator

### FRONT

Front form:	square
Front bezel material:	Plastic
Front bezel colour:	White
Front dimension:	18,8 mm x 18,8 mm

### MOUNTING

Design:	PCB
---------	-----

### OPERATING-/INDICATION PART

Lens illumination:	illuminative
Lens material:	Plastic
Lens colour:	Yellow
Illumination colour:	Yellow
Lens shape:	flush
Lens optics:	transparent

### ELECTRICAL CHARACTERISTICS

Electrostatic discharge (ESD):	15 kV
Electric strength:	500 VAC, 50 Hz, 1 minute according to IEC 60512-5-9c
Electrical lifetime:	500 000 cycles of operation at 42VDC, 50mA, according to IEC 6512-5-9c
Switching voltage and switching current:	

Switching voltage	min. 50 m VAC/DC max. 42 VAC/DC
Switching current	min. 10 µA AC/DC max. 100 mA AC/DC
Power rating	max. 2 W

## MECHANICAL CHARACTERISTIC

<b>Operating Travel:</b>	ca. 0.4 mm switching element
<b>Weight:</b>	0.003 kg
<b>Switching action:</b>	Momentary
<b>Switching system:</b>	Short-travel switching system with 2 independent contact points Guarantees reliable switching even of very light loads. Fitted with 1 normally open contact.
<b>Switching system:</b>	Short-travel element
<b>Operating force:</b>	2.7 N ±1 N switching element, 5 N lens
<b>Tightening torque:</b>	Fixing nut max. 0.5 Nm, Fixing screw mounting flange 0.4 Nm
<b>Mechanical lifetime:</b>	≥1 Mio. cycles of operation

## AMBIENT CONDITION

<b>Storage temperature:</b>	– 40 °C ... + 80 °C
<b>Shock resistance:</b>	Max. 500 m/s <sup>2</sup> , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
<b>Operating temperature:</b>	– 25 °C ... + 70 °C
<b>Vibration resistance:</b>	Max. 100 m / s <sup>2</sup> from 10 Hz ... 500 Hz, 10 cycles, 3-axis (sinusoidal EN IEC 60068-2-6)
<b>IP Protection:</b>	IP67 front side


## CERTIFICATE

<b>Conformities:</b>	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
<b>Approbations:</b>	CQC


## OTHER

<b>Dimension:</b>	18.8 mm x 18.8 mm
<b>Housing material:</b>	Plastic
<b>Short Description:</b>	Actuator, 18,8 mm x 18,8 mm, flush, illuminative, Yellow, Plastic, transparent, square, White, Plastic, Momentary, Yellow
<b>Housing colour:</b>	White

### Mounting cut-outs:



### Dimension drawings:



### Wiring diagrams:

