



1. FIGURE AND DIMENSIONS (图示及尺寸)



2. CIRCUIT DIAGRAM(接线图)



A端点位图

3. Final examination(成品检查)

- 1) 100%外形尺寸:所有尺寸与图示一致.
- 2) 外观:a)电线圆实平滑,颜色均匀,外被表面无破损、划伤、脏污、变形等缺陷;
- 3) 结构:线材和各插头五金以及各接触件应牢固无松动,标志清晰,正确无误;
- 4) 导通性能:100%测试,DC300V,绝缘 $\geq 20\text{M}\Omega$,导通电阻 $< 1\Omega$,无断路或触不良现象,测试时应加摇摆测试.

序列号	名称	规格	数量	备注
1	胶壳	X1251HM-02-N0	2PCS	
2	端子	X1251T-PSN	4PCS	
4	线缆	UL1571/28AWG	2PCS	裁线长度：210MM

					DRAWING NO.		RVE.	
					X1251T-02-A28RB-L200-F		A0	
					UNIT			
RVE.	DESCRIPTION				DATE			
DESIGNED		DATE			SCALE	Free		
CHECKED		DATE		PAGE	1 OF 1			
APPROVED		DATE						