









|                         |                                     |           |
|-------------------------|-------------------------------------|-----------|
| 17 70 000 3004          | 4,0±0,4                             | 0,7±0,05  |
| 17 70 000 3003          | 3,2±0,4                             | 1,5±0,05  |
| 17 70 000 3002          | 2,4±0,4                             | 2,3±0,05  |
| 17 70 000 3001          | 1,6±0,4                             | 3,1±0,05  |
| Bestell Nr.<br>part-no. | LP-Dicke<br>board thickness<br>[mm] | a<br>[mm] |

|                                                                                                                                     |          |       |                                                        |          |      |                                                                                       |                                                             |             |
|-------------------------------------------------------------------------------------------------------------------------------------|----------|-------|--------------------------------------------------------|----------|------|---------------------------------------------------------------------------------------|-------------------------------------------------------------|-------------|
|  All Dimensions in mm<br>Original Size DIN A 3 |          |       | Techn. Character.                                      |          |      | Nicht tolerierte Maße/Free size tolerances<br>IEC 61076-4-101                         |                                                             |             |
|                                                                                                                                     |          |       |                                                        | Dat.     | Name | Maßstab/Scale<br>2:1                                                                  | har-bus HM Übergaberahmen Typ C<br>har-bus HM Shroud Type C |             |
|                                                                                                                                     |          |       | Detail.                                                | 03.11.99 | Wei. |                                                                                       |                                                             |             |
|                                                                                                                                     |          |       | Insp.                                                  | 03.11.99 | Pa.  |                                                                                       |                                                             |             |
|                                                                                                                                     |          |       | Stand.                                                 |          |      |                                                                                       |                                                             |             |
| 34650                                                                                                                               | 05.02.08 | Hage. | HARTING Electronics GmbH & Co. KG<br>D-32339 ESPELKAMP |          |      |  | TB 17 70 000 300x                                           |             |
| 27538                                                                                                                               | 18.02.00 | HL.   |                                                        |          |      |                                                                                       |                                                             |             |
| 26972                                                                                                                               | 22.11.99 | Wei.  |                                                        |          |      |                                                                                       |                                                             |             |
| 25705                                                                                                                               |          |       |                                                        |          |      |                                                                                       |                                                             |             |
| Mod.                                                                                                                                | Dat.     | Name  |                                                        |          |      | Sub.                                                                                  |                                                             | Blatt/ page |