

450-001
Qwik-Ty® Strain Relief - Connector Designator F
 Rotatable Coupling (Straight, 45° and 90° Elbows)




45


**CONNECTOR
 DESIGNATOR
 F**

Product Series — **450**
 Connector Designator — **F**
 Angle and Profile — **S**
 Basic Part Number — **001**
 Finish (Table II) — **M**
 Shell Size (Table I) — **16**
 Ground Lug (Omit for none) — **G**


A = 90°
 B = 45°
 S = Straight



**STRAIGHT
 ROTATABLE COUPLING**



**45°
 ROTATABLE COUPLING**



**90°
 ROTATABLE COUPLING**

See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: DIMENSIONS							
Shell Size	E Cable Entry	F Max	G Max	H Max			
08	.264 (6.7)	.866 (22.0)	1.066 (27.1)	.890 (22.6)			
10	.392 (10.0)	.866 (22.0)	1.066 (27.1)	.950 (24.1)			
12	.506 (12.9)	.926 (23.5)	1.066 (27.1)	1.010 (25.7)			
14	.631 (16.0)	1.106 (28.1)	1.188 (30.2)	1.330 (33.8)			
16	.756 (19.2)	1.106 (28.1)	1.226 (31.1)	1.390 (35.3)			
18	.845 (21.5)	1.176 (29.9)	1.226 (31.1)	1.460 (37.1)			
20	.970 (24.6)	1.306 (33.2)	1.226 (31.1)	1.510 (38.4)			
22	1.095 (27.8)	1.426 (36.2)	1.226 (31.1)	1.510 (38.4)			
24	1.220 (31.0)	1.556 (39.5)	1.226 (31.1)	1.640 (41.7)			

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable. Dimensions are not intended for inspection criteria.
2. Metric dimensions (mm) are indicated in parentheses.